

## Garant

### Driven tool, radial, standard pin, VX3, Type: 30-VX3LIKD



#### Order data

Order number	319933 30-VX3LIKD
GTIN	
Item class	31W

#### Description

##### Version:

Standard alignment rail (pin).

Version IKD – with ceramic seal set, pressures up to 70 bar, with full dry-run capability.

For use on **radial turrets**. Left-hand version, i.e. machining in the direction of the main spindle.

Ratio 1:1. Version with internal cooling (internal) max. 70 bar.

For use on all **DMG Gildemeister CTX** CNC lathes with **Sauter** turret. Drive coupling **DIN 5480**.

Clamping of tools in driven tool using ER collet with external nut or VARIA VX quick-change system under license from EWS. External cooling via a coolant tube, internal cooling through the tool centrally through the spindle. Maximum speed 8000 rpm.

##### Advantage:

- **Weight- and geometry-optimized design.**
- **Process reliability through high-quality components, longevity.**
- **High torque transmission.**
- **100% control – each driven tool is subjected to a run-in programme.**
- **Internal cooling: specially developed and patented seal.**

##### Application:

As many machining steps as possible in one clamping set-up. Where space (available clamping positions) in the revolver is at a premium.

##### Suitable for:

DMG Gildemeister CTX. In some cases, Emco, Hardinge, Monforts, Scherer etc. with DIN 5480.

##### Supplied with:

Driven tool for collet: including clamping nut and hook spanner. Driven tool VARIA VX: including chuck key.

**Optional extras:**

Suitable inserts Varia VX No. 319802 – 319888, ER quick-change adapters No. 319761 – 319781, ER collets No. 308941 – 309878, ER clamping wrenches No. 309680 – 309745.

**Note:**

- **Other drive types (such as DIN 5482), ratios, dimensions, BMT etc. on request, see: [www.hoffmann.ews-tools.com](http://www.hoffmann.ews-tools.com)**
- **IC tools (with through cooling) will not run dry with standard seal, coolant filtering < 50 µm.**
- **Recommendation: Tighten version VARIA VX with a torque tool (max. 6 Nm).**
- **For heavy-duty milling work, a variant with tapered roller bearings is recommended on request.**

## Technical description

Cooling	internal
h <sub>1</sub>	68 mm
b <sub>1</sub>	69.5 mm
b <sub>2</sub>	46 mm
l <sub>1</sub>	134 mm
x	100 mm
Adapter	VX3
VDI size	30
Tool clamping	Varia VX3
Type of product	Driven tool

## Accessories

Varia collet chuck VARIA VX3 for ER collet size 25	319802 25
Varia collet chuck VARIA VX3 for ER collet size 32	319802 32
Varia collet chuck VARIA VX3 for ER collet size 20	319802 20
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 12 mm	319823 12

Indexable drill toolholder VARIA VX3 Clamping range Ø D1 20 mm	319823 20
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 6 mm	319823 6
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 16 mm	319823 16
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 27 mm	319835 27
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 16 mm	319835 16
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 10 mm	319823 10
Varia collet chuck VARIA VX3 for ER collet size 16	319802 16
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 22 mm	319835 22
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 8 mm	319823 8
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 25 mm	319823 25