

Garant
ER hydraulic collet with external thread ER25, Ød: 12mm

Order data

Order number	319746 12
GTIN	4062406244071
Item class	31W

Description
Version:

High flexibility for use with turning in static collet holders, but also when using driven tools. Best run-out characteristics.

For driven tools with internal threads.

Advantage:

- **Ideal damping characteristics, resulting in optimum component surfaces. and increased tool life.**
- **Quick and easy handling.**
- **Flexible use of reducing adapters.**
- **Perfect centring.**

Application:

Suitable for drilling, reaming, countersinking and also for use of boring bars.

Ø d₂: 42 mm

Length L: 51 mm

Thread M: M32×1.5

Technical description

Ø d ₂	42 mm
Ø d	12 mm

Thread M	M32×1.5
Length L	51 mm
Type of product	Clamping head