

Garant
Driven tool, radial, TOEM rail, VX4, Type: 40-VX4LIKD

Order data

Order number	319949 40-VX4LIKD
GTIN	
Item class	31W

Description
Version:

For use on **disc turrets**. Left-hand version, i.e. machining in the direction of the main spindle.

Ratio 1:1. Version with internal cooling (internal) max. 70 bar.

For use on all **DMG Gildemeister CTX** CNC lathes with **Sauter** turret. Drive coupling **DIN 5480**.

Clamping of tools in driven tool using ER collet with external nut or VARIA VX quick-change system under license from EWS. External cooling via a coolant tube, internal cooling through the tool centrally through the spindle. Maximum speed 8000 rpm.

Version IKD – with ceramic seal set, pressures up to 70 bar, with full dry-run capability.

Stop rail (42.5 TOEM).

Advantage:

- **Weight- and geometry-optimized design.**
- **Process reliability through high-quality components, longevity.**
- **High torque transmission.**
- **100% control – each driven tool is subjected to a run-in programme.**
- **Internal cooling: specially developed and patented seal.**

Application:

As many machining steps as possible in one clamping set-up. Where space (available clamping positions) in the revolver is at a premium.

Suitable for:

DMG Gildemeister CTX. In some cases, Emco, Hardinge, Monforts, Scherer etc. with DIN 5480.

Supplied with:

Driven tool for collet: including clamping nut and hook spanner. Driven tool VARIA VX: including chuck key.

Optional extras:

Suitable inserts Varia VX No. 319802 – 319888, ER quick-change adapters No. 319761 – 319781, ER collets No. 308941 – 309878, ER clamping wrenches No. 309680 – 309745.

Note:

- **Other drive types (such as DIN 5482), ratios, dimensions, BMT etc. on request, see: www.hoffmann.ews-tools.com**
- **IC tools (with through cooling) will not run dry with standard seal, coolant filtering < 50 µm.**
- **Recommendation: Tighten version VARIA VX with a torque tool (max. 6 Nm).**
- **For heavy-duty milling work, a variant with tapered roller bearings is recommended on request.**

Technical description

x	100 mm
b ₁	76.5 mm
Cooling	internal
b ₂	72 mm
l ₁	138 mm
h ₁	76 mm
Adapter	VX4
VDI size	40
Tool clamping	Varia VX4
Type of product	Driven tool

Accessories

Indexable drill toolholder VARIA VX4 Clamping range Ø D1 12 mm	319827 12
Indexable drill toolholder VARIA VX4 Clamping range Ø D1 10 mm	319827 10
Indexable drill toolholder VARIA VX4 Clamping range Ø D1 6 mm	319827 6

Indexable drill toolholder VARIA VX4 Clamping range \varnothing D1 25 mm	319827 25
Indexable drill toolholder VARIA VX4 Clamping range \varnothing D1 16 mm	319827 16
Axial milling cutter spigot VARIA VX4 Spigot \varnothing d1 22 mm	319838 22
Indexable drill toolholder VARIA VX4 Clamping range \varnothing D1 20 mm	319827 20
Axial milling cutter spigot VARIA VX4 Spigot \varnothing d1 16 mm	319838 16
Varia collet chuck VARIA VX4 for ER collet size 32	319804 32
Varia collet chuck VARIA VX4 for ER collet size 20	319804 20
Varia collet chuck VARIA VX4 for ER collet size 40	319804 40
Varia collet chuck VARIA VX4 for ER collet size 16	319804 16
Varia collet chuck VARIA VX4 for ER collet size 25	319804 25
Axial milling cutter spigot VARIA VX4 Spigot \varnothing d1 27 mm	319838 27
Indexable drill toolholder VARIA VX4 Clamping range \varnothing D1 8 mm	319827 8