

Garant

Face mill arbor Form ADB with cooling channel bore, SK 40 A = 200, Spigot Ø d1: 40mm



Order data

Order number	301075 40
GTIN	4062406242138
Item class	31A

Description

Version:

- With 4 cooling channel bores.
- All shanks hard turned (for smooth running!).
- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Technical description

Milling mandrel length L_4	27 mm
External Ø D	89 mm
Suitable toggle spanner No. 309840	40
Spare milling cutter lock screw No. 309860 / 309861	40
Overhang dimension A	200 mm

Data sheet

Spigot Ø d ₁	40 mm
Clamping Ø D ₁	40 mm
Adapter	SK 40 A = 200
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Milling head arbor