

## Garant

### Side lock arbor Form AD, BT 30 short, Clamping range $\varnothing$ D1: 20mm



#### Order data

Order number	303610 20
GTIN	4062406250102
Item class	31A

#### Description

##### Version:

All shanks hard turned (for smooth running!).

##### Advantage:

**The double contact between the taper** and the flat flange creates a more stable and precise clamping situation:

- **Better surface quality**
- **Longer tool life times**
- **Consistent seating in the headstock (even at high speeds)**
- **Smaller radial run-out**

A BT double contact arbor can also be used in a standard BT machine spindle – and vice versa. The advantages of the double contact are however achieved only when a double contact arbor and double contact spindle are used together.

##### Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

##### Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

#### Technical description

External $\varnothing$ D	52 mm
Spare clamping screw No. 30 9900	20
Overhang dimension A	70 mm

Clamping $\varnothing D_1$	20 mm
a	1 mm
Adapter	BT 30 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Version	BT-DC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping $\varnothing D1$ 20 mm	309900 20
--	-----------