

Garant**ER collet chuck Form AD, BT 40 short, for ER collet size: 32****Order data**

Order number	303710 32
GTIN	4062406250331
Item class	31A

Description**Version:**

Taper ground internally and externally. All shanks hard turned (for smooth running!). With RFID/Balluffchip bore.

- **High-quality precision clamping nut.**
- **Clamping nut balanced for HSM (G2.5/25,000 rpm).**
- **Optimum wear characteristics and torque transmission due to the coated precision clamping nut.**

Advantage:

The double contact between the taper and the flat flange creates a more stable and precise clamping situation:

- **Better surface quality**
- **Longer tool life times**
- **Consistent seating in the headstock (even at high speeds)**
- **Smaller radial run-out**

A BT double contact arbor can also be used in a standard BT machine spindle – and vice versa. The advantages of the double contact are however achieved only when a double contact arbor and double contact spindle are used together.

Application:

For clamping tools with parallel shank in collets to **DIN 6499 Form A and B.**

Supplied with:

ER clamping nut.

Optional extras:

ER collets No. 308881 – 309434, ER chuck keys No. 309680 – 309720 or 613300, ER clamping nut 309610.

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Note:

Matching clamping nut No. 309580 or 309610.

Technical description

for ER collets	32
Clamping range	2 - 20 mm
Overhang dimension A	70 mm
External \varnothing D	50 mm
a	1 mm
Spare ER clamping nut No. 309580	32
ER chuck key No. 309680	32
Clamping \varnothing D ₁	2-20 mm
Adapter	BT 40 short
Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Version	BT-DC
Balluffchip bore	yes
Type of product	Collet chuck

Accessories

ER chuck key for ER collet chuck 32	309680 32
-------------------------------------	-----------