

**Garant****ER hydraulic collet with external thread ER25, Ød: 16mm****Order data**

Order number	319746 16
GTIN	4062406244088
Item class	31W

**Description****Version:**

High flexibility for use with turning in static collet holders, but also when using driven tools. Best run-out characteristics.

For driven tools with internal threads.

**Advantage:**

- **Ideal damping characteristics, resulting in optimum component surfaces. and increased tool life.**
- **Quick and easy handling.**
- **Flexible use of reducing adapters.**
- **Perfect centring.**

**Application:**

Suitable for drilling, reaming, countersinking and also for use of boring bars.

**Technical description**

Ø d <sub>2</sub>	46 mm
Thread M	M32×1.5
Length L	49 mm
Ø d	16 mm

Type of product

Collet