



Face mill arbor Form A, SK 40 short, Spigot \varnothing d1: 16mm



Order data

| | |
|--------------|---------------|
| Order number | 301017 16 |
| GTIN | 4062406251864 |
| Item class | 32A |

Description

Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.

All shanks fine bead blasted.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Technical description

| | |
|---|-------|
| External \varnothing D | 38 mm |
| Overhang dimension A | 35 mm |
| Suitable toggle spanner No. 309840 | 16 |
| Spare milling cutter lock screw No. 309860 / 309861 | 16 |
| Spigot \varnothing d ₁ | 16 mm |
| Milling mandrel length L ₄ | 17 mm |

| | |
|---------------------------------------|----------------------|
| Clamping $\varnothing D_1$ | 16 mm |
| Adapter | SK 40 short |
| Standard | DIN 6357 |
| Arbor standard | ISO 7388-1 |
| Shape | ADB |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |
| Concentricity | $\leq 5 \mu\text{m}$ |
| Machining strategy | HPC |
| Type of product | Milling head arbor |