



Face mill arbor Form A, SK 50 short, Spigot \varnothing d1: 50mm



Order data

Order number	301097 50
GTIN	4062406251994
Item class	32A

Description

Version:

- **Taper shank, spigot, and all contact surfaces are ground at the collar.**
- **Short series.**
- **Increased collar contact surface.**
- **With RFID/Balluffchip bore.**

All shanks fine bead blasted.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Technical description

Spare milling cutter lock screw No. 309860 / 309861	50
Spigot \varnothing d ₁	50 mm
Suitable toggle spanner No. 309840	50
Overhang dimension A	70 mm
External \varnothing D	128 mm
Milling mandrel length L ₄	30 mm

Clamping $\varnothing D_1$	50 mm
Adapter	SK 50 short
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor