



## Pneumatic impact wrench 3/8 inch – 1/2 inch, Type: 7749



### Order data

Order number	079202 7749
GTIN	015451593339
Item class	03R

### Description

#### Version:

Robust impact wrench with **convenient one-hand changeover using Side-2-Side technology**, composite casing with thermal insulation properties and robust double hammer impact drive. Balanced weight distribution for more comfortable working. Exhaust air is directed downwards through the handle. **Tightening power can be regulated in steps.**

Torque range: 135 - 704 N·m

Maximum screw Ø (8.8 - 12.9): M24

maximum speed: 7000 min<sup>-1</sup>

Tool arbor drive profile: Square

Tool arbor size: 1/2 in

maximum air consumption: 540 l/min

### Technical description

Tool arbor drive profile	Square
maximum vibration to EN	10.9 m/s <sup>2</sup>
Tool arbor size	1/2 in

## Data sheet

maximum air consumption	540 l/min
Length	171 mm
Torque range	135 - 704 N·m
Maximum screw Ø (8.8 - 12.9)	M24
Weight	1.8 kg
Manufacturer's designation	7749
Operating noise	95 dB(A)
recommended hose size (internal Ø)	10 mm
maximum speed	7000 min <sup>-1</sup>
Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Screwdriver