



## Solid carbide milling cutter with chip separators TPC, TiAlN, Ø f8 DC: 8mm



### Order data

Order number	203101 8
GTIN	4062406252533
Item class	12X

### Description

#### Version:

High-performance milling cutter with **irregular cutter spacing** and **irregular helical pitch**. Optimised bending strength due to the use of ultra-fine grain substrates. **Chip breakers for controlled chip breaking.**

#### Note:

$h_{\max}$ : The values stated in the table are maximum values.

$a_{e \max} = 0.07 \times D$  for TPC machining.

### Technical description

Overhang length $L_1$ incl. recess	30 mm
Flute length $L_c$	24 mm
Shank Ø $D_s$	8 mm
Recess Ø $D_1$	7.8 mm
Overall length $L$	68 mm
Direction of infeed	horizontal and oblique
Helix angle	40 degrees
Cutting edge Ø $D_c$	8 mm
Average chip thickness $h_{\max}$ for TPC milling in INOX < 900 N/mm <sup>2</sup>	0.042 mm
Corner chamfer width at 45°	0.16 mm
Tolerance nominal Ø	f8

## Data sheet

Balance quality with shank	G 2.5 with HB
Shank	DIN 6535 HB to h6
No. of teeth Z	5
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	$0.07 \times D$
Through-coolant	no
Machining strategy	TPC
Colour ring	blue
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	380 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	340 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	300 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	230 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	240 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	170 m/min	M
wet maximum	Suitable		
wet minimum	Suitable only under restricted conditions		
Air	suitable		