

Garant

GARANT Master Alu solid carbide milling cutter with more chip separators TPC, DLC, Ø h6 DC: 5mm



Order data

Order number	203113 5
GTIN	4062406245740
Item class	11X

Description

Version:

Specially designed for TPC high-performance milling. **Optimised bending strength** due to the use of ultra-fine grain substrates. **1xD** chip separator for controlled chip breaking.

Balanced for very high process reliability and protecting the machine at high speeds.

Application:

Especially for milling **aluminium and non-ferrous metals**.

Note:

h_{max} : The values stated in the table are maximum values.

$ae_{max} = 0.15 \times D$ for TPC machining.

Technical description

Shank form	HA
Shank	DIN 6535 HA to h6
Average chip thickness h_{max} for TPC milling in short-chipping aluminium	0.036 mm
Overhang length L_1 incl. recess	24 mm
Direction of infeed	horizontal and oblique
Recess $\varnothing D_1$	4.5 mm
No. of teeth Z	4
Helix angle	38 degrees

Balance quality with shank	G 2.5 with HA
Overall length L	65 mm
Tolerance nominal \varnothing	h6
Flute length L_c	17 mm
Shank $\varnothing D_s$	6 mm
Cutting edge $\varnothing D_c$	5 mm
Corner rounding r_v	0.05 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.15×D
Through-coolant	no
Machining strategy	TPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	550 m/min	N
Aluminium (short chipping)	suitable	500 m/min	N
Alu > 10% Si	Suitable	450 m/min	N
PMMA acrylic	Suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N
PEEK	Suitable	150 m/min	N

PF 31	Suitable	130 m/min	N
PVDF GF20	Suitable	180 m/min	N
POM GF25	Suitable	160 m/min	N
PA 66 GF30	Suitable	150 m/min	N
PEEK GF30	Suitable	130 m/min	N
PTFE CF25	Suitable	160 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	300 m/min	N
Cu	Suitable	160 m/min	N
CuZn	suitable	200 m/min	N
wet maximum	Suitable		
wet minimum	Suitable only under restricted conditions		
dry	suitable		
Air	Suitable		

Services

Shank grinding Type HB

129100 HB