


CNMG 160608, Grade: HBT130

Order data

Order number	250204 HBT130
GTIN	4062406256180
Item class	22D

Description

CNMG 160608 HBT130 Grade: HBT130
 Chip breaker: MM
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.12 - 0.45 mm/rev.
 Cutting speed v_c main application: 50 - 200 m/min

Technical description

Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Grade	HBT130
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Number of changes/inserts	4
ISO code indexable insert	CNMG 160608
Cutting depth a_p	0.5 - 5 mm

Tool material	Carbide
Cutting speed v_c main application	50 - 200 m/min
Main application	M
Coating	TiCN
Chip breaker	MM
Feed f	0.12 - 0.45 mm/rev.
Type of product	Indexable insert for turning