

**Solid carbide milling cutter, TiAlN, Ø h10 DC: 8mm****Order data**

Order number	203248 8
GTIN	4062406253813
Item class	12X

Description**Version:**

Strengthened core and geometry for hard machining, without dynamic helical pitch. Tolerance:
Size nominal Ø D_c **0/-0.02 mm.**

Application:

For profile milling as finishing.

(Plunge cutting only to shallow depths).

Note:

Successor product to No. 203320.

Technical description

No. of teeth Z	6
Shank	DIN 6535 HA to h6
Shank Ø D _s	8 mm
Corner chamfer width at 45°	0.08 mm
Feed f _z for side milling in steel < 55 HRC	0.03 mm
Cutting edge Ø D _c	8 mm
Direction of infeed	horizontal and oblique
Flute length L _c	24 mm
Overall length L	68 mm
Helix angle	45 degrees

Tolerance nominal \varnothing	0 / -0.02
Corner chamfer angle	90 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Cutting width a_e for milling operation	0.05×D for side milling
Through-coolant	no
Colour ring	red
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable	160 m/min	P
Steel < 1100 N/mm ²	suitable	95 m/min	P
Steel < 1400 N/mm ²	suitable	85 m/min	P
Steel < 50 HRC	suitable	75 m/min	H
Steel < 55 HRC	suitable	65 m/min	H
Steel < 60 HRC	suitable	50 m/min	H
Steel < 65 HRC	suitable only under restricted conditions	30 m/min	H
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------