



## Solid carbide high performance drill Whistle-Notch shank DIN 6535 HE, TiAlN, Ø DC m7: 10,3mm



### Order data

Order number	122668 10,3
GTIN	4062406254483
Item class	12E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Through-coolant: yes, with 25 bar

Standard: DIN 6537

Tolerance nominal Ø: m7

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 55.3 mm

Tolerance nominal Ø: m7

Overall length L: 118 mm

Shank Ø  $D_s$ : 12 mm

Feed f in stainless steel < 900 N/mm<sup>2</sup>: 0.12 mm/rev.

### Technical description

Number of cutting edges Z	2
Overall length L	118 mm
Tolerance nominal Ø	m7
Shank Ø $D_s$	12 mm
Shank tolerance	h6
recommended maximum drilling depth $L_2$	55.3 mm

Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.12 mm/rev.
Nominal Ø D <sub>c</sub>	10.3 mm
Standard	DIN 6537
Flute length L <sub>c</sub>	71 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	140°
Shank	DIN 6535 HE to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	45 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	40 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	32 m/min	S
GG	suitable only under restricted conditions	70 m/min	K

Uni	suitable
wet maximum	suitable
wet minimum	suitable
Air	suitable