



CNMG 120404, Grade: HBT020

Order data

Order number	250196 HBT020
GTIN	4062406256135
Item class	22D

Description

CNMG 120404 HBT020 Grade: HBT020
 Chip breaker: PM
 Cutting depth a_p : 0.8 - 5 mm
 Feed f : 0.1 - 0.45 mm/rev.
 Cutting speed v_c main application: 100 - 280 m/min

Technical description

Cutting speed v_c main application	100 - 280 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Grade	HBT020
Cutting depth a_p	0.8 - 5 mm
Main application	P
Chip breaker	PM
Cutting conditions	slightly interrupted

Number of changes/inserts	4
Feed f	0.1 - 0.45 mm/rev.
Tool material	Carbide
Corner radius	0.4 mm
Coating	TiCN
ISO code indexable insert	CNMG 120404
Type of product	Indexable insert for turning