


**WNMG 080408, Grade: HBT130****Order data**

Order number	252095 HBT130
GTIN	4062406256852
Item class	22D

Description

WNMG 080408 HBT130 Grade: HBT130
Chip breaker: MM
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.12 - 0.45 mm/rev.
Cutting speed v_c main application: 50 - 200 m/min

Technical description

Coating	TiCN
Cutting depth a_p	0.5 - 5 mm
Feed f	0.12 - 0.45 mm/rev.
Cutting conditions	slightly interrupted
Cutting speed v_c main application	50 - 200 m/min
ISO code indexable insert	WNMG 080408
Corner radius	0.8 mm

Main application	M
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Number of changes/inserts	6
Grade	HBT130
Chip breaker	MM
Tool material	Carbide
Type of product	Indexable insert for turning