



**DCMT 11T304, Grade: HBT020**

**Order data**

Order number	260378 HBT020
GTIN	4062406257095
Item class	22D

**Description**

DCMT 11T304 HBT020 Grade: HBT020  
 Chip breaker: PF  
 Cutting depth  $a_p$ : 0.4 - 1.5 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 120 - 330 m/min

**Technical description**

Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Cutting speed $v_c$ main application	120 - 330 m/min
Feed $f$	0.1 - 0.3 mm/rev.
Chip breaker	PF
Cutting conditions	slightly interrupted
Number of changes/inserts	2

Grade	HBT020
Cutting depth $a_p$	0.4 - 1.5 mm
Tool material	Carbide
Main application	P
Coating	TiCN
ISO code indexable insert	DCMT 11T304
Type of product	Indexable insert for turning