



DNMG 150608, Grade: HBT020

Order data

Order number	250786 HBT020
GTIN	4062406256531
Item class	22D

Description

DNMG 150608 HBT020 Grade: HBT020
 Chip breaker: PR
 Cutting depth a_p : 1.8 - 6 mm
 Feed f : 0.2 - 0.6 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Feed f	0.2 - 0.6 mm/rev.
Grade	HBT020
Cutting speed v_c main application	80 - 260 m/min
Chip breaker	PR
ISO code indexable insert	DNMG 150608
Main application	P
Cutting conditions	slightly interrupted

Coating	TiCN
Corner radius	0.8 mm
Cutting depth a_p	1.8 - 6 mm
Finishing/roughing assignment	Roughing
Tool material	Carbide
Number of changes/inserts	4
Type of product	Indexable insert for turning