


**TCMT 16T304, Grade: HBT020****Order data**

Order number	261018 HBT020
GTIN	4062406257538
Item class	22D

Description

TCMT 16T304 HBT020 Grade: HBT020
Chip breaker: PM
Cutting depth a_p : 0.5 - 2.5 mm
Feed f : 0.12 - 0.3 mm/rev.
Cutting speed v_c main application: 100 - 280 m/min

Technical description

Feed f	0.12 - 0.3 mm/rev.
Cutting conditions	slightly interrupted
Main application	P
Cutting speed v_c main application	100 - 280 m/min
Tool material	Carbide
Chip breaker	PM
ISO code indexable insert	TCMT 16T304
Number of changes/inserts	3

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Coating	TiCN
Corner radius	0.4 mm
Grade	HBT020
Cutting depth a_p	0.5 - 2.5 mm
Type of product	Indexable insert for turning