


CCMT 120404, Grade: HBT130

Order data

Order number	260088 HBT130
GTIN	4062406256944
Item class	22D

Description

CCMT 120404 HBT130 Grade: HBT130
 Chip breaker: M
 Cutting depth a_p : 0.1 - 1 mm
 Feed f : 0.05 - 0.2 mm/rev.
 Cutting speed v_c main application: 60 - 220 m/min

Technical description

Cutting conditions	slightly interrupted
Grade	HBT130
Cutting speed v_c main application	60 - 220 m/min
Corner radius	0.4 mm
Number of changes/inserts	2
Chip breaker	M
Finishing/roughing assignment	Finishing

Cutting depth a_p	0.1 - 1 mm
ISO code indexable insert	CCMT 120404
Tool material	Carbide
Feed f	0.05 - 0.2 mm/rev.
Coating	TiCN
Main application	M
Type of product	Indexable insert for turning