



DCMT 11T308, Grade: HBT130



Order data

Order number	260508 HBT130
GTIN	4062406257361
Item class	22D

Description

DCMT 11T308 HBT130 Grade: HBT130
 Chip breaker: MM
 Cutting depth a_p : 0.3 - 2.5 mm
 Feed f : 0.05 - 0.35 mm/rev.
 Cutting speed v_c main application: 50 - 200 m/min

Technical description

Number of changes/inserts	2
Main application	M
Corner radius	0.8 mm
Feed f	0.05 - 0.35 mm/rev.
Chip breaker	MM
Grade	HBT130
Coating	TiCN

Cutting depth a_p	0.3 - 2.5 mm
Cutting conditions	slightly interrupted
ISO code indexable insert	DCMT 11T308
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Cutting speed v_c main application	50 - 200 m/min
Type of product	Indexable insert for turning