

Garant
eco clamping toolholder, right-hand, Shank / insert size: 20/08mm

Order data

Order number	251900 20/08
GTIN	4045197809025
Item class	21U

Description
Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

With flank face cooling.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

Through-coolant: yes

ISO code toolholder: DWLNR/L 2020K08

suitable indexable insert: WN.. 0804..

Functional width L₄: 25 mm

Head length L₁: 32 mm

Overall length L: 125 mm

Shim: 259033 6

Technical description

ISO code toolholder	DWLNR/L 2020K08
suitable indexable insert	WN.. 0804..
Overall length L	125 mm
Functional width L ₄	25 mm
Clamp, screw, spring	259036 10

Insert size	8 mm
Head length L ₁	32 mm
Shim screw	259027 4
Shim	259033 6
Shank size	20 mm
Series	Eco
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
--	------------