

**Garant****Eco clamping toolholder DWLNR 95°, for indexable inserts WN., right-hand****Order data**

|              |               |
|--------------|---------------|
| Order number | 251900 25/08  |
| GTIN         | 4045197809032 |
| Item class   | 21U           |

**Description****Version:**

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

With flank face cooling.

**Note:**

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

**Technical description**

|                                 |                 |
|---------------------------------|-----------------|
| ISO code toolholder             | DWLNR/L 2525M08 |
| Overall length L                | 150 mm          |
| Head length L <sub>1</sub>      | 32 mm           |
| Shim                            | 259033 6        |
| Shank size                      | 25 mm           |
| Functional width L <sub>4</sub> | 32 mm           |
| suitable indexable insert       | WN.. 0804..     |
| Shim screw                      | 259027 4        |
| Clamp, screw, spring            | 259036 10       |

## Data sheet

|                        |                               |
|------------------------|-------------------------------|
| Insert size            | 8 mm                          |
| Series                 | Eco                           |
| Application type       | right-hand                    |
| Through-coolant        | yes                           |
| Setting angle $\kappa$ | 95 degrees                    |
| Application            | External longitudinal turning |
| Application            | External longitudinal turning |
| Type of product        | Boring bar                    |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/251900-25/08>