

GECHTER**Hand lever toggle press with pneumatic assistance, Compressive force: 12 kN****Order data**

Order number

086761 12

GTIN

Item class

08V

Description**Version:**

HKP/L-DS hand lever press with compressed air assistance and defined 12kN start.

Compressive force 12 kN (operating pressure 7.7 bar).

The press slides are extended via a manual lever with toggle action. In this position the worker by pressing a button or optionally by a slight rotary movement of the manual lever trigger a defined pneumatic compression stroke of length 5.9 mm.

Application:

Pressing, riveting, punching, swaging, driving in.

Throat: 120 mm

Installation height: 73 - 240 mm

Mounting hole in the slide ram: Ø 15 H7 mm

Table width: 200 mm

Table depth: 169 mm

Height without hand lever: 729 mm

Technical description

Throat

120 mm

Table depth	169 mm
Mounting hole in the slide ram	Ø 15 H7 mm
Table width	200 mm
Footprint depth	260 mm
Footprint width	340 mm
Weight	40 kg
Installation height	73 - 240 mm
Height without hand lever	729 mm
maximum compressive force	12 kN
Operating pressure	2 - 7 bar
Stroke length	7 - 46 mm
Thread of the compressed air connection port	1/4 inch
Type of product	Toggle lever press