

## HEDI

### Machine / workstation lamp, Type: 9LED-BR



#### Order data

Order number	081300 9LED-BR
GTIN	4003644022540
Item class	08B

#### Description

**Version:**

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

**Robust, long, coated flexible metal arm** for good mobility of the lamp head and high stability. Workbench lamp with **3 brightness levels** for optimised illumination of the workplace. Innovative design permits assessment of the object from above using the lamp - extended 600 mm flexible shaft.

**Standard:**

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

· **Sturdy, long, coated flexible metal arm.**

**Function:**

IP20: Protected against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and offers no protection against water.

**Supplied with:**

Bulb, with **strong magnetic clamp, 50 mm screw-on clamp, and mounting screws** for machine, table, wall or ceiling attachment.

IP Index of Protection: IP 20

Light output: 9 W

Illumination: 514 lm

Connection cable length: 3 m

## Technical description

Bulb	LED
Lamp replaceable	no
ATEX zone	no
Power supply	Mains-powered
Connection cable length	3 m
Nominal voltage	230 V
Light output	9 W
Spread angle	100 degrees
IP Index of Protection	IP 20
Illumination	514 lm
Type of product	Workplace light