

**Battery charging cabinet BATTERY CHARGE, Model: CHA**

Order data

Order number	981114 CHA
GTIN	
Item class	96G

Description**Version:**

Cabinet shell made from sheet metal with permanent self-closing using oil-damped door closer, 3-level door retention component.

- **Can be closed with a profile cylinder (compatible with integrated locking systems) and closing status display (red/green). Not compatible with the Hoffmann locking system.**
- **Integrated transport base for internal transport.**
- **Integrated adjustable feet for compensating for unevenness in the floor.**
- **90-minute fire protection from the outside inwards (type 90/type tested according to EN 14470-1) and over 90 minutes of fire resistance time from the inside outwards in the event of fire exposure.**
- **Safety plug in order to easily disconnect from the power supply.**

Battery charging cabinet for safe charging and storage of lithium-ion batteries. Open two cabinet doors simultaneously with

just one hand. Extraction unit to prevent heat build-up during battery charging. Pressure relief opening

in the top section. Installed 3-level warning and fire suppression system including smoke detector, temperature sensor, optical

and acoustic alarm triggering and fire suppression unit; automatically triggered in the event of fire; with plug in order to connect to the power supply. Socket strip with metal housing and 8

protective contact sockets for each storage level mounted completely operational in the cabinet interior.

Standard:

DIN EN 14470-1 und DIN EN 1363-1

Supplied with:

Cabinet with 5 perforated storage shelves incl. socket strips, 1 floor-level containment tray, sheet metal, powder-coated.

Colour:

Cabinet casing RAL 7016 anthracite grey, doors gentian blue RAL 5010, **powder-coated.**

Note:

At regular intervals (annually), cordless storage and charging cabinets should be maintained and their operating characteristics checked by an authorised competent person. We recommend fitting on a level ground for easy evacuation of the safety cabinets.

Technical description

Depth	615 mm
Usable width	1050 mm
Height	2224 mm
Number of floor-level containment trays	1
Width	1193 mm
Internal dimension at intake: height	90 mm
Usable height	1647 mm
Weight	512 kg
Internal dimension at intake: width	1120 mm
maximum loading	600 kg
Number of shelves	5
Usable depth	522 mm
Volume of floor-level drip tray	33 l
Nominal voltage	400 V
Height adjustment interval	32 mm
Fire resistance	90 min
Type of product	Safety cabinet

