


**WNMG 080412, Grade: HBT130**

**Order data**

Order number	252226 HBT130
GTIN	4062406258146
Item class	22D

**Description**

WNMG 080412 HBT130 Grade: HBT130  
 Chip breaker: MR  
 Cutting depth  $a_p$ : 2 - 6 mm  
 Feed  $f$ : 0.15 - 0.55 mm/rev.  
 Cutting speed  $v_c$  main application: 40 - 180 m/min

**Technical description**

Finishing/roughing assignment	Roughing
Grade	HBT130
ISO code indexable insert	WNMG 080412
Feed $f$	0.15 - 0.55 mm/rev.
Main application	M
Number of changes/inserts	6
Coating	TiCN

Cutting speed $v_c$ main application	40 - 180 m/min
Tool material	Carbide
Cutting conditions	slightly interrupted
Corner radius	1.2 mm
Chip breaker	MR
Cutting depth $a_p$	2 - 6 mm
Type of product	Indexable insert for turning