



## Battery charger, Type: 4.2PRO



### Order data

Order number	081590 4.2PRO
GTIN	4013674144624
Item class	08C

### Description

#### Version:

Microprocessor-controlled charging and servicing stations for battery cells with **individual channel monitoring** and battery fault detection. Status display for each charging slot, automatic charging switch-off, overload protection and **trickle charging**. Input voltage 100–240 V. With LC display for detailed monitoring of the charging process. Additional USB-A charging output 5 V, 1000 mA, mains plug (100 - 240 V).

#### Application:

**NiMH/NiCd battery charging points:** 1-4 × Micro AAA / Mignon AA or 1-3 × Baby C or 1-2 × Mono D.

#### Attention:

German version. Order free UK adapter plug No. 08 1172\_GB

Interface: Digimatic interface

Nominal voltage: 100 - 240 V

maximum charging current: 1.8 A

Maximum number of charging points: 4

Number of charging slots for USB: 1

Length: 130 mm

Width: 80 mm

### Technical description

maximum charging current	1.8 A
--------------------------	-------

Number of charging slots for USB	1
Length	130 mm
Maximum number of charging points	4
Width	80 mm
Height	31 mm
Nominal voltage	100 - 240 V
Interface	Digimatic interface
Type of product	Battery charger