



**HOLEX Pro Steel solid carbide roughing end mill HPC, TiAlN, Ø d11 DC: 16mm**

**Order data**

Order number	205706 16
GTIN	4062406262495
Item class	12X

**Description**
**Version:**

Dimensions similar to DIN 6527. **Optimised special knuckle form profile for roughing.** Very **high metal removal rate.**

**Application:**

For roughing machining, particularly suitable for full-slot machining.

**Technical description**

Direction of infeed	horizontal, oblique and vertical
Tolerance nominal Ø	d11
Shank	DIN 6535 HB to h6
Recess Ø D <sub>1</sub>	14.8 mm
Overhang length L <sub>1</sub> incl. recess	42 mm
Shank Ø D <sub>s</sub>	16 mm
Cutting edge Ø D <sub>c</sub>	16 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.09 mm
Overall length L	92 mm
No. of teeth Z	5
Corner chamfer width at 45°	0.8 mm
Flute length L <sub>c</sub>	32 mm

Corner chamfer angle	45 degrees
Helix angle	45 degrees
Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.08 mm
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	135 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	120 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	60 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	45 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	suitable only under restricted conditions
Air	Suitable only under restricted conditions