




Switchable welding aid, Type: QHCSS



Order data

| | |
|--------------|---------------|
| Order number | 085957 QHCSS |
| GTIN | 5012095618072 |
| Item class | 08Q |

Description

Version:

Holds workpieces at angles of 45° and 90°. Temperature-resistant up to maximum 180 °C. Ideal for round and rectangular hollow section, and also for angle material and flat material.

Technical description

| | |
|--------------------------------|--------------------|
| Length | 111 mm |
| maximum temperature resistance | 180 °C |
| Width | 29 mm |
| Weight | 0.7 kg |
| Nominal clamping force | 400 N |
| Height | 95 mm |
| Type of product | Magnet with switch |