

GECHTER**Hand lever toggle press with pneumatic assistance, Compressive force: 4 kN****Order data**

Order number

086761 4

GTIN

Item class

08V

Description**Version:**

HKP/L-DS hand lever press with compressed air assistance and defined 4kN start.

Compressive force 4 kN (operating pressure 7.7 bar).

The press slides are extended via a manual lever with toggle action. In this position the worker by pressing a button or optionally by a slight rotary movement of the manual lever trigger a defined pneumatic compression stroke of length 5.9 mm.

Application:

Pressing, riveting, punching, swaging, driving in.

Throat: 120 mm

Installation height: 73 - 240 mm

Mounting hole in the slide ram: Ø 10 H7 mm

Table width: 200 mm

Table depth: 169 mm

Height without hand lever: 678 mm

Technical description

Weight

36 kg

Throat	120 mm
Footprint width	340 mm
Footprint depth	260 mm
Height without hand lever	678 mm
Installation height	73 - 240 mm
Mounting hole in the slide ram	Ø 10 H7 mm
Table width	200 mm
Table depth	169 mm
maximum compressive force	4 kN
Operating pressure	2 - 7 bar
Thread of the compressed air connection port	1/4 inch
Stroke length	6 - 46 mm
Type of product	Toggle lever press