

**KERN****Crane scales type HCD, maximum weighing range: 150kg**

## Order data

Order number	479434 150
GTIN	4045761214149
Item class	47D

## Description

**Version:**

Back-lit LCD display, easily read even from afar. Data hold function for retaining the display value. High mobility thanks to stable lightweight design. Battery lasts approx. 20 hours.

**Supplied with:**

Including remote control with 2 batteries No. 081561 size LR3. Scales including 4 batteries No. 081561 LR6.

## Technical description

Body depth	79 mm
Error limit from maximum value	0.2 %
Article no of the battery / rechargeable battery fitted	081561 LR3
Operating temperature	0 - 40 °C
Calibration	Price on request
Net weight	1.1 kg
Overall length	276 mm

Number of batteries contained	2
Body height	97 mm
Scale divisions	50 g
Body width	194 mm
maximum weighing range	150 kg
Power supply	Battery-powered
Display backlit	yes
Data storage key	yes
Battery working life	20 h
Type of product	Suspended scales / crane scales

---

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------