

**HOLEX**

**Solid carbide high performance drill, plain shank DIN 6535 HA, TiN, Ø DC h7 (mm or inch): 5,1**



## Order data

Order number	122310 5,1
GTIN	4045197043610
Item class	12E

## Description

### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**NEW GENERATION AVAILABLE!**

**Recommended successor product is No. 122501.**

Versions HB and HE supplied at the same price as HA.

**Form HB:** order with **No. 122315**.

**Form HE:** order with **No. 122320**.

## Technical description

Nominal Ø $D_c$	5.1 mm
Feed $f$ in steel $< 900 \text{ N/mm}^2$	0.14 mm/rev.
Flute length $L_c$	28 mm
Shank tolerance	h6
Number of cutting edges $Z$	2
Tolerance nominal Ø	h7
Shank Ø $D_s$	6 mm
Overall length $L$	66 mm

Standard	DIN 6537 K
recommended maximum drilling depth L <sub>2</sub>	20.4 mm
Coating	TiN
Tool material	Solid carbide
Version	4×D
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Semi-Standard	yes
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
GG(G)	suitable only under restricted conditions	70 m/min	K
wet maximum	suitable		
dry	suitable		

