

**Garant****Carbide-tipped hammer drill SDS-plus, Ø×overall length: 8X160mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 789010 8X160  |
| GTIN         | 4062406262532 |
| Item class   | 71C           |

**Description****Version:**

The distinctive and aggressive centre point permits active centring and optimum guidance during the drilling operation. Innovative head design with short straight lands for significantly faster drilling coupled with significantly improved stability, even in reinforced concrete. Vibration-optimised helical profile with reinforced core. The core diameter and the helix pitch of the drill are precisely matched to each other and ensure efficient transmission of force from the hammer drill to the carbide tip.

**Advantage:**

- **Short helical lands and concave rake faces (scooping effect) ensure smooth evacuation of the drilling dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **Additional specially shaped core cutting edges: efficient fragmentation of concrete.**

**Application:**

For drilling concrete, natural stone, and masonry - with very high drilling comfort.

**Note:**

When using extra long drills (> 500 mm), first drill a pilot hole with a shorter drill of the same diameter (prevents bending and breakage).

**Technical description**

|                           |        |
|---------------------------|--------|
| Number of cutting edges Z | 2      |
| Ø                         | 8 mm   |
| Flute length              | 100 mm |
| overall length            | 160 mm |

|                                  |                 |
|----------------------------------|-----------------|
| Tool material                    | Carbide         |
| Use with impact / without impact | Impact drilling |
| Shank                            | SDS Plus        |
| Type of product                  | Masonry drill   |