



Switchable welding aid, Type: QHCSL



Order data

| | |
|--------------|---------------|
| Order number | 085957 QHCSL |
| GTIN | 5012095618089 |
| Item class | 08Q |

Description

Version:

Holds workpieces at angles of 45° and 90°. Temperature-resistant up to maximum 180 °C. Ideal for round and rectangular hollow section, and also for angle material and flat material.

Technical description

| | |
|--------------------------------|--------------------|
| Weight | 1.4 kg |
| Length | 152 mm |
| Width | 35 mm |
| Height | 130 mm |
| maximum temperature resistance | 180 °C |
| Nominal clamping force | 750 N |
| Type of product | Magnet with switch |

