

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: QC/28

Order data

Order number	264835 QC/28
GTIN	4251414902770
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: STUCL

suitable indexable insert: TC.. 1102..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 24 mm

Centre offset L_3 : 13 mm

Technical description

Cutting point / joint	20 mm
Approach angle	93 °

Minimum pre-drill $\varnothing D_{\min}$	24 mm
Series	Master Mute
ISO code cutting head	STUCL
suitable indexable insert	TC.. 1102..
Overall length L	20 mm
Insert screw	269023 2
System	QC
Centre offset L_3	13 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Clamping screw	269407
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Insert screw Type 4	269022 4
Insert screw Type 2	269023 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500