

Garant**GARANT Master Mute cutting head, left-hand, System / insert size: QC/29****Order data**

Order number	264835 QC/29
GTIN	4251414902794
Item class	29D

Description**Suitable for:**

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: STUCL

suitable indexable insert: TC.. 16T3..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 26 mm

Centre offset L_3 : 15 mm

Technical description

Overall length L	21 mm
Series	Master Mute

Insert screw	269023 2
Cutting point / joint	20 mm
System	QC
ISO code cutting head	STUCL
Approach angle	93 °
suitable indexable insert	TC.. 16T3..
Minimum pre-drill $\varnothing D_{\min}$	26 mm
Centre offset L_3	15 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Insert screw Type 2	269023 2
Clamping screw	269432
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15