

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: QC/30**

**Order data**

Order number	264834 QC/30
GTIN	4251414902947
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264890; 264894 and 264898.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SVUCR

suitable indexable insert: VC.. 1103..

Approach angle: 93 °

Minimum pre-drill  $\varnothing D_{\min}$ : 26 mm

Centre offset  $L_3$ : 16 mm

**Technical description**

ISO code cutting head	SVUCR
Series	Master Mute

System	QC
Overall length L	20 mm
suitable indexable insert	VC.. 1103..
Insert screw	269023 1
Centre offset L <sub>3</sub>	16 mm
Minimum pre-drill $\varnothing D_{\min}$	26 mm
Cutting point / joint	20 mm
Approach angle	93 °
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Insert screw Type 1	269023 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Set of insert screws 10 pieces	269413
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500