

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: DM/40**

**Order data**

Order number	264838 DM/40
GTIN	
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	48 mm
Overall length L	35 mm
Approach angle	95 degrees
Shim	259033 2
Shim screw	259027 2
suitable indexable insert	CN.. 1204..
ISO code cutting head	DCLNR

Series	Master Mute
Clamp, screw, O-ring	259036 3
Centre offset L <sub>3</sub>	27 mm
System	DM
Cutting point / joint	40 mm
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

---

## Accessories

Shim screw Type 2	259027 2
Shim Type 2	259033 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10