

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: DM/48

Order data

Order number	264838 DM/48
GTIN	4251414902480
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SDUCR

suitable indexable insert: DC.. 11T3..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre offset L_3 : 27 mm

Technical description

Shim	269007 1
Approach angle	93 °

Centre offset L ₃	27 mm
Overall length L	32 mm
Cutting point / joint	40 mm
Series	Master Mute
Shim screw	269015 2
Minimum pre-drill Ø D _{min}	49 mm
System	DM
suitable indexable insert	DC.. 11T3..
Insert screw	269023 3
ISO code cutting head	SDUCR
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamping screw	269433
Insert screw Type 3	269023 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500