

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: DM/50

Order data

Order number	264838 DM/50
GTIN	
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Technical description

ISO code cutting head	SVUCR
suitable indexable insert	VC.. 1604..
Centre offset L ₃	27 mm
Approach angle	93 °
Insert screw	269023 3
Shim screw	269015 2
Shim	259033 5

Series	Master Mute
Overall length L	32 mm
System	DM
Cutting point / joint	40 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Insert screw Type 1	269023 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500