

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: QC/23

Order data

Order number	264835 QC/23
GTIN	4251414902619
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SDQCL

suitable indexable insert: DC.. 11T3..

Approach angle: 107.5 °

Minimum pre-drill $\varnothing D_{\min}$: 26 mm

Centre offset L_3 : 15 mm

Technical description

Centre offset L_3	15 mm
System	QC

Overall length L	22 mm
ISO code cutting head	SDQCL
Series	Master Mute
Minimum pre-drill $\varnothing D_{\min}$	26 mm
Insert screw	269023 2
Approach angle	107.5 °
suitable indexable insert	DC.. 11T3..
Cutting point / joint	20 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Insert screw Type 2	269023 2
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Clamping screw	269432
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500