

**Garant**
**GARANT Master Mute cutting head, left-hand, System / insert size: QC/20**

**Order data**

Order number	264835 QC/20
GTIN	4251414902435
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264890; 264894 and 264898.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SCLCL

suitable indexable insert: CC.. 09T3..

Approach angle: 95 °

Minimum pre-drill  $\varnothing D_{\min}$ : 24 mm

Centre offset  $L_3$ : 13 mm

**Technical description**

suitable indexable insert	CC.. 09T3..
ISO code cutting head	SCLCL

Insert screw	269023 2
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Overall length L	20 mm
Centre offset $L_3$	13 mm
Cutting point / joint	20 mm
Approach angle	95 °
Series	Master Mute
System	QC
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Insert screw Type 2	269023 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Insert screw Type 3	269022 3
Clamping screw	269406
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500