

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: QC/23

Order data

Order number	264834 QC/23
GTIN	4251414902527
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SDQCR

suitable indexable insert: DC.. 11T3..

Approach angle: 107.5 °

Minimum pre-drill $\varnothing D_{\min}$: 26 mm

Centre offset L_3 : 15 mm

Technical description

Overall length L	22 mm
ISO code cutting head	SDQCR

Minimum pre-drill $\varnothing D_{\min}$	26 mm
Approach angle	107.5 °
Cutting point / joint	20 mm
Series	Master Mute
suitable indexable insert	DC.. 11T3..
Insert screw	269023 2
Centre offset L_3	15 mm
System	QC
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Insert screw Type 2	269023 2
Clamping screw	269432
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500