

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: QC/22

Order data

Order number	264835 QC/22
GTIN	4251414902596
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SDQCL

suitable indexable insert: DC.. 0702..

Approach angle: 107.5 °

Minimum pre-drill $\varnothing D_{\min}$: 24 mm

Centre offset L_3 : 13 mm

Technical description

Insert screw	269023 1
Series	Master Mute

System	QC
Cutting point / joint	20 mm
Centre offset L ₃	13 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Approach angle	107.5 °
ISO code cutting head	SDQCL
Overall length L	20 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Insert screw Type 1	269023 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Clamping screw	269431
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500