

Garant
GARANT Master Mute cutting head, right-hand, System / insert size: ST/1

Order data

Order number	264826 ST/1
GTIN	2050002058118
Item class	29D

Description
Suitable for :

Boring bar shanks No. 320102; 320103; 320407 and 320408.

Through-coolant: yes

Cutting point / joint: 25 mm

ISO code indexable cutting head: PCLNR

suitable indexable insert: CN.. 1204..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 32 mm

Centre offset L_3 : 17 mm

Technical description

Cutting point / joint	25 mm
Shim	320610 P01
Insert size	12 mm
Lever	320612 P01
suitable indexable insert	CN.. 1204..

Centre offset L ₃	17 mm
ISO code cutting head	PCLNR
Minimum pre-drill Ø D _{min}	32 mm
Overall length L	35 mm
Insert assignment	left-hand and neutral
Spring pin	320618 P01
Lever screw	320611 P01
Approach angle	95 °
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Clamping screw No. 3 Type P01	320611 P01
Toggle lever No. 4 Type P01	320612 P01
Intermediate spacer No. 1 Type P01	320610 P01
Tube pin No. 7 Type P01	320618 P01