

Garant

Jobber drill extra long HSS N, uncoated, Ø DC h8 × overall length L: 10,5X340mm



Order data

Order number	116245 10,5X340
GTIN	4062406264826
Item class	11B

Description

Version:

With precision ground point.

Vaporised high performance drills for drilling particularly deep holes. Take particular care to ensure **frequent chip clearance**.

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability

Technical description

Feed f in steel < 750 N/mm ²	0.1 mm/rev.
recommended maximum drilling depth L ₂	219.3 mm
Tolerance nominal Ø	h8
Shank Ø D _s	10.5 mm
Overall length L	340 mm
Nominal Ø D _c	10.5 mm
Number of cutting edges Z	2
Flute length L _c	235 mm
Standard	DIN 1869

Point angle	118 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS
Type	N
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	50 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	32 m/min	N
Steel < 500 N/mm ²	suitable	28 m/min	P
Steel < 750 N/mm ²	suitable	21 m/min	P
Steel < 900 N/mm ²	suitable	18 m/min	P
Steel < 1100 N/mm ²	suitable	5 m/min	P
GG(G)	suitable	18 m/min	K
Oil	suitable		
wet maximum	suitable		