

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: QC/29**

**Order data**

Order number	264834 QC/29
GTIN	4251414902749
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264890; 264894 and 264898.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: STUCR

suitable indexable insert: TC.. 16T3..

Approach angle: 93 °

Minimum pre-drill  $\varnothing D_{\min}$ : 26 mm

Centre offset  $L_3$ : 15 mm

**Technical description**

Overall length L	21 mm
suitable indexable insert	TC.. 16T3..

Insert screw	269023 2
ISO code cutting head	STUCR
Centre offset L <sub>3</sub>	15 mm
Series	Master Mute
Cutting point / joint	20 mm
Approach angle	93 °
System	QC
Minimum pre-drill Ø D <sub>min</sub>	26 mm
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Insert screw Type 2	269023 2
Clamping screw	269432