

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: QC/30

Order data

Order number	264835 QC/30
GTIN	4251414902978
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264890; 264894 and 264898.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: QC

Cutting point / joint: 20 mm

ISO code cutting head: SVUCL

suitable indexable insert: VC.. 1103..

Approach angle: 93°

Minimum pre-drill $\varnothing D_{\min}$: 26 mm

Centre offset L_3 : 16 mm

Technical description

Approach angle	93°
Centre offset L_3	16 mm

suitable indexable insert	VC.. 1103..
System	QC
ISO code cutting head	SVUCL
Cutting point / joint	20 mm
Insert screw	269023 1
Minimum pre-drill $\varnothing D_{\min}$	26 mm
Overall length L	20 mm
Series	Master Mute
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Insert screw Type 1	269023 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Set of insert screws 10 pieces	269413
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500